

CRX-3iA



Max. load capacity
at wrist: 3kg



Max. reach
(end of flange):
692 mm

FANUC

Robot			Max load capacity at wrist (kg)	****Reach (mm)	Controlled axes	**Repeatability (mm)	Mechanical weight (kg)	Motion range [°]						*Maximum speed (mm/s)		***Allowable Wrist Load			Input power source (VAC)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	Collaborative Mode	High Speed Mode	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia		Body standard	Wrist & J3 arm
CRX	iA	3	3	692	6	±0.02	11	400	360	592	380	360	450	1200	2500	8.5/0.32	6.5/0.24	4/0.08	100-120 200-240	IP67	IP67


● standard ○ on request - not available * During short distance, it may not reach the maximum value stated. Please set motion speed according to risk assessment of system. ** Based on ISO9283 ***Nm/Kg.m² ****At the end of flange

CRX-3iA


Standard model



CRX-3iA



END OF FLANGE



OPERATING
SPACE OF
END OF FLANGE
(J4=+90 DEG)